

### CLIP BATHING SLING – PADDED LEGS

The Clip bathing sling – padded legs is suitable for bathing and showering as the mesh material allows water to pass easily through the sling. It has additional padding around the legs area to provide extra comfort.

| PRODUCT INFORMATION   |                                 |
|-----------------------|---------------------------------|
| <b>ARTICLE NUMBER</b> | <b>MAA4061M</b>                 |
| Safe working load     | 272 kg (600 lbs)                |
| Size                  | XS S M L LL XL XXL              |
| Morphology            |                                 |
| Cleaning method       |                                 |
| Material              | Knitted polyester fabric - mesh |

#### COMPATIBLE LIFTS

- |   |  |
|---|--|
| <b>Floor lifts</b>  | <b>Ceiling lifts</b>   |
| <ul style="list-style-type: none"> <li>Maxi Move</li> <li>Maxi Twin</li> <li>Maxi Twin compact</li> <li>Maxi 500</li> </ul> | <ul style="list-style-type: none"> <li>Maxi Sky 2 Series</li> <li>Maxi Sky 2 Plus (Single mode)</li> </ul> |



### CLIP BATHING SLING – UNPADDED AND EXTENDED LEGS

The Clip bathing sling – unpadded and extended legs is suitable for bathing and showering as the mesh material allows water to pass easily through the sling. The extended leg sling has been designed to create a longer reach around the thighs if needed.

| PRODUCT INFORMATION   |                                 |
|-----------------------|---------------------------------|
| <b>ARTICLE NUMBER</b> | <b>MAA4160M</b>                 |
| Safe working load     | 272 kg (600 lbs)                |
| Size <sup>(1)</sup>   | XS S M L LL XL XXL              |
| Morphology            |                                 |
| Cleaning method       |                                 |
| Material              | Knitted polyester fabric - mesh |

#### COMPATIBLE LIFTS

- |   |  |
|---|--|
| <b>Floor lifts</b>  | <b>Ceiling lifts</b>   |
| <ul style="list-style-type: none"> <li>Maxi Move</li> <li>Maxi Twin</li> <li>Maxi Twin compact</li> <li>Maxi 500</li> </ul> | <ul style="list-style-type: none"> <li>Maxi Sky 2 Series</li> <li>Maxi Sky 2 Plus (Single mode)</li> </ul> |



### CLIP IN SITU SLING – UNPADDED LEGS

The Clip in situ sling – unpadded legs is suitable for everyday patient handling activities, such as bed and chair-related transfers. It may be left under the patient between transfers (if clinical assessment allows).

| PRODUCT INFORMATION |                        |
|---------------------|------------------------|
| <b>Part number</b>  | <b>MAA2040M</b>        |
| Safe working load   | 190 kg (418 lbs)       |
| Size                | XS S M L LL XL XXL     |
| Morphology          |                        |
| Cleaning method     |                        |
| Material            | Polyester woven fabric |

#### COMPATIBLE LIFTS

- |   |  |
|---|--|
| <b>Floor lifts</b>  | <b>Ceiling lifts</b>   |
| <ul style="list-style-type: none"> <li>Maxi Move</li> <li>Maxi Twin</li> <li>Maxi Twin compact</li> <li>Maxi 500</li> </ul> | <ul style="list-style-type: none"> <li>Maxi Sky 2 Series</li> <li>Maxi Sky 2 Plus (Single mode)</li> </ul> |



### CLIP BATHING IN SITU SLING – UNPADDED LEGS

The Clip bathing in situ sling – unpadded legs is suitable for bathing and showering activities as the mesh material allows water to pass easily through the sling.

| PRODUCT INFORMATION   |   |
|-----------------------|---|
| <b>ARTICLE NUMBER</b> | <b>MAA2070M</b>                             |
| Safe working load     | 190 kg (418 lbs)                            |
| Size                  | XS S M L LL XL XXL                          |
| Morphology            |   |
| Cleaning method       |   |
| Material              | Lightweight knitted polyester fabric - mesh |

#### COMPATIBLE LIFTS

- |   |  |
|---|--|
| <b>Floor lifts</b>  | <b>Ceiling lifts</b>   |
| <ul style="list-style-type: none"> <li>Maxi Move</li> <li>Maxi Twin</li> <li>Maxi Twin compact</li> <li>Maxi 500</li> </ul> | <ul style="list-style-type: none"> <li>Maxi Sky 2 Series</li> <li>Maxi Sky 2 Plus (Single mode)</li> </ul> |

